Formulating a Greener World®

HydraJET® 2030R Aqueous ink for semi-porous media







TECHNICAL DATA SHEET

HydraJET[®] 2030R red aqueous TIJ 2.5 ink consists of FDA approved FD&C dyes. HydraJET[®] 2030R ink provides eye-catching color, crisp and sharp text, logo and barcode, and fast drying time on semi-porous substrates. ⁽¹⁾

Technical Specifications

	HydraJET [®] 2030R Print Cartridge
Ink type	Red dye aqueous ink
Print cartridge type	HP 45ai
Resolution	Up to 600 dpi, recommended 300 $ imes$ 300 dpi
Nozzle count	300
Print swath	12.7 mm
Firing voltage	11.0 V
Fire pulse width	1.8 μs
Pulse warming	OFF
Decap time ⁽¹⁾	lh
Drying time ⁽¹⁾	1 – 3 s at 300 × 300 dpi on coated paper
Throw distance ⁽²⁾	Up to 3 mm, recommended 1 mm
Average delivered ink	40 mL (vertical)
Average drop volume	27 pL
Operating conditions	15 °C to 35 °C, 35% to 80% RH
Shipping / storage temperature	10 °C to 35 °C
Best before ⁽³⁾	12 months from filling date

Cartridge Shipping & Storage

- Store the cartridge with a clip placed over the printhead. Nozzles up or horizontal.
- Refer to Safety Data Sheet for more information.

Cartridge Maintenance & Handling

- Use a lint-free cloth moistened with deionized water to clean the cartridge printhead.
- Holding the cartridge printhead face down, gently press the printhead on a lint-free cloth to allow ink to wick out. Then, slowly and lightly wipe across the tip of the long edge.
- Do not shake the cartridge.

Ordering Information

Product number	Product description
2030R42A	HydraJET® 2030R Print Cartridge

(1) Ink performance may vary depending on substrate, printer, and environmental conditions.

(2) Recommended. May vary by application.

(3) Must be shipped and stored under recommended conditions.

MYLAN GROUP Longduc Industrial Park, Travinh City, Travinh Province, Vietnam Tel.: +84 2943 846 997 - Fax: +84 2943 846 998 Email: inks@mylangroup.com Website: www.mylangroup.com